





3 way valve for calibration and drip tray for measuring jar



Ecolab diaphragm pumps with overpressure safety valves and/or snubbers against pressure shocks



Integrated manifold



Dedicated flowmeter or rotameter for each product line



Quick acting leak detection

ELADOS Pump Rack

The Dispensing Solution for Tunnel Washers

MAIN FEATURES

- ◆ Up to 9 Ecolab diaphragm pumps (Turbo Pumps or EMP Pumps)
- ◆ Integrated flow meters for precise metering with optional line strainer for PVC oval gear meter (in use with raw material)
- ◆ Optimised to work with the new Ecolab *my Control* PLC and information management systems
- ◆ Dedicated groups for alkaline products (in PP) and acid products (in PVDF)
- ◆ Integrated drip tray with leakage alarm and separation between alkaline and acid products
- ◆ Integrated 3 way valves in each line for calibration and safety
- ◆ Flush valve block with connected manifolds or option to use single flush extensions

BENEFITS

- ◆ Quick installation
- ◆ Space saving
Dimensions: 2050 mm x 1700 mm x 560 mm (W / H / D)
- ◆ Electric devices have no contact to chemicals
- ◆ Compliant with CE, RoHS II and WEEE requirements